# Temperature Controller

**E5CX(-H)** 

1/16 DIN, Multi-Range Controller Offers Advanced PID Control

- Advanced PID control provides fast, stable response without overshoot
- Large, easy-to-read displays show both process temperature and set value
- High accuracy with selectable temperature ranges
- Heater burnout alarm types are also available
- 3-year warranty





# Ordering Information \_

# **■ TEMPERATURE CONTROLLERS**

Models with heater burnout alarm use a single alarm output for the nine-function temperature alarm and heater burnout alarm. A current transformer is not included with the temperature controller with heater burnout alarm. Be sure to order it separately, as required. To order models factoy-set to Celsius, drop the "F" from the part number.

Input type	Heater burnout alarm	Control output type	Part number
Thermocouple	No	Relay output	E5CX-RTC-F
		Voltage output	E5CX-QTC-F
		Current output	E5CX-CTC-F
	Yes	Relay output	E5CX-RHTC-F
		Voltage output	E5CX-QHTC-F
Platinum RTD	No	Relay output	E5CX-RP-F
		Voltage output	E5CX-QP-F
		Current output	E5CX-CP-F
	Yes	Relay output	E5CX-RHP-F
		Voltage output	E5CX-QHP-F

### **■ TEMPERATURE RANGES**

# Thermocouple Types

Input type		Thermocouple	Thermocouple							
(switch selectable)		Туре К	Type J/L	Type T/U	Type E	Type B	Type N	Type R	Type S	
Temperature	°C	-200 to 1,300	-100 to 850	-200 to 400	0 to 600	100 to 1,800	0 to 1,300	0 to 1,700	0 to 1,700	
range	۰F	-300 to 2,300	-100 to 1,500	-300 to 700	0 to 1,100	300 to 3,200	0 to 2,300	0 to 3,000	0 to 3,000	
Unit of measure		1° C or F, mai	1° C or F, main setting and alarm							

### **Platinum RTD Types**

Input type		Platinum RTD		
(switch selectable)		100 Ω		
Temperature	°C	-99.9 to 450		
range °F		-99.9 to 800		
Unit of measure		0.1° C or F, main setting and alarm		

### **■ CURRENT TRANSFORMERS**

Hole diameter	5.8 mm (0.23 in)	12.0 mm (0.47 in)
	E54-CT1	E54-CT3

### **■ REPLACEMENT PARTS**


Description	Part number
Adapter for panel mounting (supplied with each unit)	Y92F-30


# Advanced PID Control

Omron utilizes an advanced PID algorithm which provides superior control during both start-up and normal operation.

In classic PID, there is a trade-off between having the controller respond quickly and accurately to the initial target value, and also to an external disturbance that may occur after the initial target value has been achieved. PID constants set to maximize performance on start-up often degrade response to external disturbances, and the converse would also be true.

With Omron's PID algorithm, start-up and disturbance response are independent of each other. The controllers' auto-tuning process determines PID constants that are optimum for disturbance response. However, on start-up the algorithm is altered by known values ( $\alpha$  and  $\beta$ ). The resulting control is responsive on start-up and stable during regular operation.





# Specifications\_\_\_\_\_

# **■ TEMPERATURE CONTROLLER**

Sensor input Supply voltage Operating vo Power consu Control	ge		Thermocouple types K, J, L, T, U, E, B, N, R, S Platinum RTD (100 Ω) 100 to 240 VAC, 50/60 Hz				
Supply voltage Operating vo Power consu	ge						
Operating vo Power consu							
Power consu			85 to 110% of rated supply voltage				
	Power consumption		Approx. 6 VA at 100 VAC to 10 VA at 240 VAC				
	Туре	Relay	SPST-NO, 3 A, 250 VAC (resistive load), E5CX-R				
output Voltage			20 mA, 12 VDC with short-circuit protection, E5CX-QQQ				
	Current		4 to 20 mA, 600 Ω max. load, E5CX-C□□				
	Isolation		All output units are optically isolated from the internal circuits.				
	Hysteresis		0.0 to 999.9°C/°F in units of 0.1 (during ON/OFF control action)				
•	Update Output		500 ms for pulse and current outputs				
	time	Display	500 ms				
Alarm	Туре		SPST-NO relay, 1 A, 250 VAC (resistive load)				
output	Setting ra	enge	Thermocouple: -999 to 9,999°C/°F				
Сара	j coungn	ango	Platinum RTD: -99.9 to 999°C/°F				
Heater	Type		SPST-NO relay, 1 A, 250 VAC (E5CX-□H□□-F)				
burnout	Setting		0.1 to 49.9 A in units of 0.1 A				
output	range		0.0 setting disables the output; 50.0 setting turns output ON continuously				
	Minimun ON time	n detectable	200 ms; heater current is not measured when the control output is ON less than 200 ms				
Indication	General		±0.3% of set value or ±1°, whichever is greater, ±1 digit maximum				
accuracy	Exceptions		Accuracy of type U thermocouples is $\pm 2^{\circ}$ C (3.6°F) from -150° to 400°C (-240° to 700°F), $\pm 1$ digit. Accuracy is not guaranteed below -150°C (-240°F). The accuracy of types R and S thermocouples is $\pm 3^{\circ}$ C ( $\pm 5.4^{\circ}$ F) from 0° to 200°C (32° to 400°F), $\pm 1$ digit.				
	Heater b	urnout	±5% of full scale, ±1 digit maximum of heater current				
Setting accuracy			Set value coincides with the indicated value, since no relative error exists between both values				
Control	Туре		ON/OFF or PID with automatic tuning and circuitry to prevent overshoot				
modes Proportional band		nal band	0.0 to 999.9°C/°F in units of 0.1				
ļ	Reset time		0 to 3,999 seconds in units of 1 second				
	Rate time		0 to 3,999 seconds in units of 1 second				
	Control period		Pulse output: 1 to 99 seconds in units of 1 second				
Sampling period		g period	500 ms				
Memory prot	ection		Non-volatile memory (EEPROM)				
Other	Input shi	ft	Offsets input value and display value to accommodate a sensor input that deviates by a known value.				
functions			Thermocouple range: -999 to 9,999°C/°F Platinum RTD range: -99.9 to 999°C/°F				
	Miscellar	neous	Upper and lower set value limits, key protection, °C/°F selectable internally, Normal and Reverse output selection, Watchdog function to detect CPU failure and restore CPU to normal operation.				
Indicators			Preset Value, 10.5 mm (0.42 in); Set Value, 7.5 mm (0.3 in); LED indicators for others				
Materials			Plastic case				
Mounting			Panel mount ·				
Connections			Plated steel screw terminals mounted on rear of unit				
Weight			Approx. 160 g (5.6 oz.)				
Enclosure	Front pa		IEC IP50, NEMA 4 with optional cover Y92A-48N				
ratings	Rear par Termina		IEC IP20				
Approvals	UL	<u> </u>	IEC IP00 Recognized, File Number E68481 (all models)				
,	CSA		Certified, File Number LR59623 (all models)				
Ambient			-10° to 55°C (14° to 131°F)				
temperature	<u> </u>		-25° to 65°C (-13° to 149°F)				
Humidity			35 to 85% RH				
Insulation resistance		·	20 MΩ minimum at 500 VDC				
Insulation res	Dielectric strength		2,000 VAC, 50/60 Hz for 1 minute between terminals of different polarity				
	engın						
		cal durability	10 to 55 Hz 0.75 mm (0.03 in) in X, Y, and Z directions for 2 hours each				
Dielectric stre	Mechani	cal durability ion durability	10 to 55 Hz 0.75 mm (0.03 in) in X, Y, and Z directions for 2 hours each 2 to 55 Hz, 2 G, in X, Y, and Z directions for 10 minutes each				
Dielectric stre	Mechani Malfunct						

# **■ CURRENT TRANSFORMER**


Heater current	Maximum 50 A continuous service, single-phase
Weight	Approx. 11.5 g (0.41 oz.) for E54-CT1; approx. 50 g (1.8 oz) for E54-CT3
Dielectric strength	1,000 VAC
Vibration	50 Hz (approximately 10G)


# Dimensions

Unit: mm (inch)

# **■ E5CX/E5CX-H TEMPERATURE CONTROLLERS**









**Panel Cutout** 

**Side-by-side Mounting of Several Temperature Controllers** 






Controllers	2	3	4	5	6
L	93.5 <sup>+1</sup> -0	141.5 <sup>+1</sup>	189.5 <sup>+1</sup> -0	237.5 <sup>+1</sup> -0	285.5 <sup>+1</sup> <sub>-0</sub>

 $L=(48 \times block -2.5)_{-0}^{+1}$ for tight side-by-side mounting

- Note: 1. Recommended panel thickness is 1 to 8 mm (0.04 to 0.31 in).
  - Because mounting brackets are attached to the top and bottom of a temperature controller, tight sideby-side mounting is possible.


### **CURRENT TRANSFORMER**

E54-CT1




E54-CT3





# Nomenclature




Key	Description	Key	Description	
1	Process Value indicator displays the process temperature and indicates the parameter being displayed on the SV (Set Value) display and error	6	When pressed, the up key increases the set temperature or other parameters. When held down, the key successively increases the value.	
	messages.	7	When pressed, the down key decreases the set	
2	Heater Burnout indicator lights when a heater burnout is detected and stays lit until rest. Provided on the		temperature or other parameters. When held down the key successively decreases the value.	
	Heater Burnout Alarm Types only.	- 8	The mode key shifts display to the next parameter.	
3	Set Value (SV) displays set temperature and other parameters.	9	Press the level key for at least 2 seconds to change levels to set different groups of parameters.	
4	Alarm indicator lights when the alarm output is ON.	10	The output indicator lights when the control output	
5	Auto-tuning key. To start auto-tuning, press the key for at least 1 second when PID operation has been		ON. There is no output indicator for Current Output Types.	
	designated. To stop auto-tuning, press the key for at least 1 second during auto-tuning.	11	The auto-tuning indicator flashes on and off about every second when auto-tuning is occurring.	


# Connections.

### **■ CONTROLLER WIRING**

### **Controllers without Heater Burnout Alarm**





### **Controllers with Heater Burnout Alarm**



# **■ OVERALL SYSTEM**

#### **Connection Example**





NOTE: DIMENSIONS SHOWN ARE IN MILLIMETERS. To convert millimeters to inches divide by 25.4.

**OMRON ELECTRONICS LLC** 

One East Commerce Drive Schaumburg, IL 60173

1-800-55-OMRON

# **OMRON ON-LINE**

Global - http://www.omron.com USA - http://www.omron.com/oei Canada - http://www.omron.com/oci **OMRON CANADA, INC.** 885 Milner Avenue

Scarborough, Ontario M1B 5V8

416-286-6465

<sup>\*</sup>This wiring must be passed through the hole of the current transformer. The current

transformer can be connected to the controller in any polarity.
\*\*For the heater burnout alarm types, the alarm output goes ON when either the normal alarm or the heater burnout alarm is activated.